



SuperSense Scale X

- Für Gasflaschen bis zu 11 Kg
- Gewichts-basierte Messung
- Signalausgabe digital via Bluetooth
- Signalausgabe analog von 0 - 2,5 Volt

Typenbezeichnung	Artikelnummer	Hinweis
SuperSense Scale X Pro	SS-SCX-30-PRO	Scale mit Montageplatte + Controller. Analoge Signalausgabe.
SuperSense Scale X Pro, Wireless	SS-SCX-30-PRO-W	Scale mit Montageplatte + Controller. Signalausgabe via integriertem Bluetooth sowie analog.

Technische Daten	
Spannungsversorgung	10 - 30 V DC
Leistungsaufnahme	ohne Bluetooth: <0,05 Watt mit Bluetooth <0,1 Watt)
Signalausgang Bluetooth	Zur Verwendung mit der SuperSense App
Signalausgang Analog	Analoges Spannungssignal von 0 - 2,5 Volt
Kalibrierung	Für Gasflaschen bis zu 11 Kg. Kalibrierung erfolgt via App oder optional auch direkt am Controller. Tara-Werte können auch hinterlegt werden - bei der App können diese flexibel geändert werden, ohne App muss der Tara-Wert ggf. beim Flaschenwechsel neu angepasst oder über eine Drittanbieterlösung („Display“) angepasst werden.

Ansprechpartner für technische Fragen

Stefan Roth
Tel. +498031.22044-65
sro@comworks.de

Josef Stuffer
Tel. +498031.22044-99
jst@comworks.de



SuperSense Laser

- For gas cylinders up to 11 kg
- Weight-based measurement
- Digital signal output via Bluetooth
- Analog signal output from 0 - 2.5 volts

Type designation	Order Number	Hinweis
SuperSense Scale X Pro	SS-SCX-30-PRO	Scale with mounting plate + controller. Analog signal output.
SuperSense Scale X Pro, Wireless	SS-SCX-30-PRO-W	Scale with mounting plate + controller. Signal output via integrated Bluetooth and analog.

Technical data	
Power supply	10 - 30 V DC
Power consumption	without Bluetooth: <0,05 Watt with Bluetooth <0,1 Watt)
Bluetooth signal output	For use with the SuperSense App
Analog signal output	Analog voltage signal from 0 - 2.5 volts
Calibration	For gas cylinders up to 11 kg. Calibration via app or optionally directly on the controller. Tare values can also be stored - with the app these can be changed flexibly, without the app the tare value may have to be readjusted when changing cylinders or adjusted via a third-party solution ("display").

Contact for technical questions

Stefan Roth
Tel. +498031.22044-65
sro@comworks.de

Josef Stuffer
Tel. +498031.22044-99
jst@comworks.de